



75143329



IP20



Technical properties

Functions

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions
Light scenes	retrieval, adjustment and storage of 8 light scenes

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
Number of buttons	3
Operation	one push-button operation for switching, pushing, shutters and dimming

Dimensions

Labelling field length (W x H)	56.4 x 17 mm
Height	71 mm
Width	71 mm

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of labelling	105,105,105
Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Material for printing	Paper
Surface appearance	velvety
Type of surface treatment	untreated
Material family	Plastic

LED control

LED	with white operation LED and 6 amber status LEDs
-----	--

Settings

Supported configuration modes	system
Parameterisation	single and two push-button operation parameterisable

Scope of delivery	
Bus connection included	Yes
Equipment	
Number of actuation points	6
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 3gang
Controller extension unit	usable as thermostat extension unit
Use	
Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 3 - Sales	with integral bus coupling unit
Safety	
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	KNX ; Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
Instructions	
Information text	Labelling field sheet, order no. 9498 31 03, available separately.