


75144229

IP20



Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With room temperature controller	No
----------------------------------	----

Function	for switch, push-button, dimmer and shutter functions
----------	-------------------------------------------------------

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--------------------------------------------

Controls and indicators

With LED indication	Yes
Number of buttons	4

Dimensions

Labelling field length (W x H)	56.4 x 12 mm
Height	71 mm
Width	71 mm

Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---------------------------------------------

Screen

With display	No
--------------	----

Materials

Colour of labelling	105,105,105
Colour of design line	polar white
Colour	polarwhite
Material for printing	Paper
Type of surface treatment	Painted
Material family	Plastic

LED control

LED	with white operation LED and 8 amber status LEDs
-----	--------------------------------------------------

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Number of actuation points	8
----------------------------	---

With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 4gang
Use	
Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 3 - Sales	with integral bus coupling unit
Safety	
Protection index IP	IP20
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker Q.1/Q.3
Secondary design line(s)	Berker Q.1 ; KNX ; Berker Q.3
Instructions	
Information text	Labelling field sheet, order no. 9498 32 04, available separately.