



75162091

**IP20**

#### Technical properties

##### Architecture

Fixing mode	flush-mounting
-------------	----------------

##### Functions

With room temperature controller	No
----------------------------------	----

Function	for switch, push-button, dimmer and shutter functions
----------	---

##### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

##### Controls and indicators

With LED indication	Yes
---------------------	-----

Number of buttons	2
-------------------	---

##### Dimensions

Depth	16.7 mm
-------	---------

Height	88.5 mm
--------	---------

Width	88.5 mm
-------	---------

##### Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

##### Screen

With display	No
--------------	----

##### Materials

Colour of design line	glass polar white
-----------------------	-------------------

Colour	polarwhite
--------	------------

Type of surface treatment	Painted
---------------------------	---------

Material family	Glass
-----------------	-------

##### LED control

LED	with blue operation LED and 4 white status LEDs (labelling field illumination)
-----	--

##### Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

##### Scope of delivery

Bus connection included	No
-------------------------	----

##### Accessories included

Box	for installation in single standard wall boxes
-----	--

### Equipment

Number of actuation points	4
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ

### Safety

Protection index IP	IP20
Protection	with dismantling protection

### Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

### Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX ; Berker B.IQ