



75162092

IP20

## B.IQ push-button 2gang, KNX - B.IQ, glass black

### Technical properties

#### Architecture

Fixing mode flush-mounting

#### Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

#### Compatibility

Extension unit extension unit for light scene push-button

#### Controls and indicators

With LED indication Yes

Number of buttons 2

#### Dimensions

Depth 16.65 mm

Assembling height 16.7 mm

Height 88.5 mm

Width 88.5 mm

#### Measurement

Value transmitter dimming / position value transmitter 1 byte

#### Screen

With display No

#### Materials

Colour of design line glass black

Colour black

RAL colour RAL 9005 - Jet black

Material glass

Type of surface treatment Painted

Material family Glass

#### LED control

LED with blue operation LED and 4 white status LEDs (labelling field illumination)

#### Connection

Bus coupling unit for bus coupling unit flush-mounted

**Scope of delivery**

Bus connection included	No
-------------------------	----

**Accessories included**

Box	for installation in single standard wall boxes
Matching products	for glass frames in the same "style" for additional applications, see the Design line B.7, for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

**Equipment**

Number of actuation points	4
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ

**Safety**

Protection index IP	IP20
Protection	with dismantling protection

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

**Identification**

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ