



75162093



IP20

B.IQ push-button 2gang, KNX - B.IQ, stainless steel, metal brushed

Technical properties

Functions

| | |
|----------------------------------|---|
| With room temperature controller | No |
| Function | for switch, push-button, dimmer and shutter functions |

Compatibility

| | |
|----------------|--|
| Extension unit | extension unit for light scene push-button |
|----------------|--|

Controls and indicators

| | |
|---------------------|-----|
| With LED indication | Yes |
| Number of buttons | 2 |

Dimensions

| | |
|-------------------|----------|
| Depth | 16.65 mm |
| Assembling height | 16.7 mm |
| Height | 88.5 mm |
| Width | 88.5 mm |

Measurement

| | |
|-------------------|---|
| Value transmitter | dimming / position value transmitter 1 byte |
|-------------------|---|

Screen

| | |
|--------------|----|
| With display | No |
|--------------|----|

Materials

| | |
|------------------------|-----------------|
| Colour of design line | Stainless steel |
| Material / workmanship | metal brushed |
| Surface appearance | matt |
| Material family | Metal |

LED control

| | |
|-----|--|
| LED | with blue operation LED and 4 white status LEDs (labelling field illumination) |
|-----|--|

Connection

| | |
|-------------------|-------------------------------------|
| Bus coupling unit | for bus coupling unit flush-mounted |
|-------------------|-------------------------------------|

Scope of delivery

| | |
|-------------------------|----|
| Bus connection included | No |
|-------------------------|----|

Accessories included

| | |
|-----|--|
| Box | for installation in single standard wall boxes |
|-----|--|

for stainless steel frames in the same "style" for additional applications, see the Design line B.7 ; for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

Matching products

Equipment

| | |
|--|--------------------|
| Number of actuation points | 4 |
| With anti-theft/dismantling protection | Yes |
| Product type: | product type: B.IQ |

Safety

| | |
|---------------|-----------------------------|
| REACH conform | Yes |
| RoHS conform | Yes |
| Protection | with dismantling protection |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...45 °C |
|-----------------------|------------|

Identification

| | |
|--------------------------|-----------------------------|
| Application, usage | KNX - operating systems |
| Product family | product family: push-button |
| Main design line | KNX - Berker B.IQ |
| Secondary design line(s) | KNX ; Berker B.IQ |