



75162189

IP20

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With room temperature controller	No
----------------------------------	----

Function	for switch, push-button, dimmer and shutter functions
----------	---

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
---------------------	-----

Number of buttons	4
-------------------	---

Connectivity

Radio	for radio wall-transmitter insert
-------	-----------------------------------

Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of design line	polar white
-----------------------	-------------

Colour	polarwhite
--------	------------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	thermoplastic
----------	---------------

Surface appearance	matt
--------------------	------

Type of surface treatment	Painted
---------------------------	---------

Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

Scope of delivery

Bus connection included	No
-------------------------	----

Equipment

Number of actuation points	4
----------------------------	---

With anti-theft/dismantling protection	Yes
--	-----

Product type:	product type: push-button 2gang
---------------	---------------------------------

Safety	
Protection index IP	IP20
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Identification	
Application, usage	Radio bus - operating systems, KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1, Berker B.7, KNX, Berker B.1, Radio bus, Berker B.3
Instructions	
Information text	Application as 7516 20..