


75162370

IP20



Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 2

Dimensions

Labelling field length (W x H) 66.8 x 25 mm

Height 55.1 mm

Width 70.5 mm

Measurement

Value transmitter dimming / position value transmitter 1 byte

Screen

With display No

Materials

Colour of design line polar white

Colour polarwhite

RAL colour RAL 9010 - Pure white

Material Plastic/metal

Material for printing Paper

Type of surface treatment untreated

Material family Plastic

LED control

LED - KNX with white operation LED and 4 red status LEDs

Connection

Bus coupling unit for bus coupling unit flush-mounted

Scope of delivery

Bus connection included

No

Equipment

Number of actuation points	4
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 2gang

Use

Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 3 - Sales	with horizontal operation

Safety

Protection index IP	IP20
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems, Radio bus - operating systems
Product family	product family: push-button
Secondary design line(s)	KNX, Radio bus, Berker K.1