




75162385

IP20



## Technical properties

### Architecture

Fixing mode flush-mounting

### Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

### Compatibility

Extension unit extension unit for light scene push-button

### Controls and indicators

With LED indication Yes

Number of buttons 2

### Connectivity

Radio for radio wall-transmitter insert

### Dimensions

Labelling field length (W x H) 52.3 x 24.9 mm

Height 55.4 mm

Width 55.6 mm

### Measurement

Value transmitter dimming / position value transmitter 1 byte

### Screen

With display No

### Materials

Colour of labelling 217,217,217

Colour independent of design lines for anthracite and aluminium

Colour aluminium/anthracite

RAL colour RAL 7021 - Black grey

Material thermoplastic

Material for printing Paper

Type of surface treatment untreated

Material family Plastic

### LED control

LED with 4 red transmission and battery status LEDs

LED - KNX with white operation LED and 4 red status LEDs

**Connection**

Bus coupling unit for bus coupling unit flush-mounted

**Scope of delivery**

Bus connection included No

**Equipment**

Number of actuation points 4

With anti-theft/dismantling protection Yes

Type of configuration Beschriftungsfeld(er) - Folie

Product type: product type: push-button 2gang

**Use**

Differentiation characteristic 1 - Sales with labelling fields

Differentiation characteristic 3 - Sales with horizontal operation

**Safety**

Protection index IP IP20

Protection with dismantling protection

**Use conditions**

Operating temperature -5...45 °C

**Identification**

Application, usage Radio bus - operating systems, KNX - operating systems

Product family product family: push-button

Main design line KNX - Berker S.1/B.3/B.7

Secondary design line(s) Berker B.1, Berker B.3, Berker B.7, Berker S.1, Radio bus, KNX