




75162385



IP20



## Technical properties

### Functions

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions

### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

### Controls and indicators

With LED indication	Yes
Number of buttons	2

### Connectivity

Radio	for radio wall-transmitter insert
-------	-----------------------------------

### Dimensions

Labelling field length (W x H)	52.3 x 24.9 mm
Height	55.4 mm
Width	55.6 mm

### Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

### Screen

With display	No
--------------	----

### Materials

Colour of labelling	217,217,217
Colour independent of design lines	for anthracite and aluminium
Material for printing	Paper
Surface appearance	glossy
Type of surface treatment	untreated
Material family	Plastic

### LED control

LED	with 4 red transmission and battery status LEDs
LED - KNX	with white operation LED and 4 red status LEDs

### Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

### Scope of delivery

Bus connection included

No

### Equipment

Number of actuation points	4
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 2gang

### Use

Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 3 - Sales	with horizontal operation

### Safety

Protection	with dismantling protection
------------	-----------------------------

### Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

### Identification

Application, usage	Radio bus - operating systems ; KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker S.1/B.3/B.7
Secondary design line(s)	Berker B.1 ; Berker B.3 ; Berker B.7 ; Berker S.1 ; Radio bus ; KNX