




75162785



Berker S.1/B.3/B.7 Push Button 2-gang, Comfort with Label, Anthracite/Aluminium

Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 2

Operation one push-button operation for switching, pushing, shutters and dimming, activation of second user level via object

Dimensions

Labelling field length (W x H) 52.3 x 24.9 mm

Height 55.4 mm

Width 55.6 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display No

Materials

Colour of labelling 217,217,217

Colour independent of design lines for anthracite and aluminium

Colour other

RAL colour RAL 7021 - Black grey

Material thermoplastic

Material for printing Paper

Type of surface treatment untreated

LED control

LED with white operation LED and 4 red status LEDs

Connection

Settings

Parameterisation	single and two push-button operation parameterisable
------------------	--

Scope of delivery

Bus connection included	No
-------------------------	----

Equipment

Number of actuation points	4
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 2gang

Use

Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 3 - Sales	with horizontal operation

Safety

Protection index IP	IP20
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	KNX, Berker S.1, Berker B.3, Berker B.7