




75163385



IP20



## Technical properties

### Functions

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions

### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

### Controls and indicators

With LED indication	Yes
Number of buttons	3

### Connectivity

Radio	for radio wall-transmitter insert
-------	-----------------------------------

### Dimensions

Labelling field length (W x H)	52.3 x 15.6 mm
Height	55.4 mm
Width	55.6 mm

### Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

### Screen

With display	No
--------------	----

### Materials

Colour of labelling	217,217,217
Colour independent of design lines	for anthracite and aluminium
Material for printing	Paper
Surface appearance	glossy
Type of surface treatment	untreated
Material family	Plastic

### LED control

LED	with 6 red transmission and battery status LEDs
LED - KNX	with white operation LED and 6 red status LEDs

### Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

### Scope of delivery

Bus connection included No

---

**Equipment**

Number of actuation points 6

With anti-theft/dismantling protection Yes

Type of configuration Beschriftungsfeld(er) - Folie

Product type: product type: push-button 3gang

---

**Use**

Differentiation characteristic 1 - Sales with labelling fields

Differentiation characteristic 3 - Sales with horizontal operation

---

**Safety**

Protection with dismantling protection

---

**Use conditions**

Operating temperature -5...45 °C

---

**Identification**

Application, usage Radio bus - operating systems ; KNX - operating systems

Product family product family: push-button

Secondary design line(s) KNX ; Radio bus ; Berker S.1 ; Berker B.3 ; Berker B.7