



75163385



IP20



Technical properties

Functions

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
Number of buttons	3

Connectivity

Radio	for radio wall-transmitter insert
-------	-----------------------------------

Dimensions

Labelling field length (W x H)	52.3 x 15.6 mm
Height	55.4 mm
Width	55.6 mm

Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of labelling	217,217,217
Colour independent of design lines	for anthracite and aluminium
Material for printing	Paper
Surface appearance	glossy
Type of surface treatment	untreated
Material family	Plastic

LED control

LED	with 6 red transmission and battery status LEDs
LED - KNX	with white operation LED and 6 red status LEDs

Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

Scope of delivery

Bus connection included No

Equipment

Number of actuation points 6

With anti-theft/dismantling protection Yes

Type of configuration Beschriftungsfeld(er) - Folie

Product type: product type: push-button 3gang

Use

Differentiation characteristic 1 - Sales with labelling fields

Differentiation characteristic 3 - Sales with horizontal operation

Safety

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C

Identification

Application, usage Radio bus - operating systems ; KNX - operating systems

Product family product family: push-button

Secondary design line(s) KNX ; Radio bus ; Berker S.1 ; Berker B.3 ; Berker B.7