



75163770



## Technical properties

### Functions

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions

### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

### Controls and indicators

With LED indication	Yes
Number of buttons	3
Operation	one push-button operation for switching, pushing, shutters and dimming ; activation of second user level via object

### Dimensions

Labelling field length (W x H)	66.8 x 15.7 mm
Height	55.1 mm
Width	70.5 mm

### Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

### Screen

With display	No
--------------	----

### Materials

Colour of labelling	105,105,105
Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Material for printing	Paper
Surface appearance	glossy
Type of surface treatment	untreated
Material family	Plastic

### LED control

LED	with white operation LED and 6 red status LEDs
-----	--

### Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

### Settings

**Scope of delivery**

Bus connection included	No
-------------------------	----

**Equipment**

Number of actuation points	6
----------------------------	---

With anti-theft/dismantling protection	Yes
--	-----

Type of configuration	Beschriftungsfeld(er) - Folie
-----------------------	-------------------------------

Product type:	product type: push-button 3gang
---------------	---------------------------------

**Use**

Differentiation characteristic 1 - Sales	with labelling fields
--	-----------------------

Differentiation characteristic 3 - Sales	with horizontal operation
--	---------------------------

**Safety**

Protection	with dismantling protection
------------	-----------------------------

Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte
-------	---

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

Storage/transport temperature	-20...70 °C (storage at > 45°C reduces the service life)
-------------------------------	--

**Identification**

Application, usage	KNX - operating systems
--------------------	-------------------------

Product family	product family: push-button
----------------	-----------------------------

Secondary design line(s)	KNX ; Berker K.1
--------------------------	------------------