


75163770



## Technical properties

### Architecture

Fixing mode flush-mounting

### Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

### Compatibility

Extension unit extension unit for light scene push-button

### Controls and indicators

With LED indication Yes

Number of buttons 3

Operation one push-button operation for switching, pushing, shutters and dimming, activation of second user level via object

### Dimensions

Labelling field length (W x H) 66.8 x 15.7 mm

Height 55.1 mm

Width 70.5 mm

### Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

### Screen

With display No

### Materials

Colour of design line polar white

Colour polarwhite

RAL colour RAL 9010 - Pure white

Material thermoplastic

Material for printing Paper

Type of surface treatment untreated

Material family Plastic

### LED control

LED with white operation LED and 6 red status LEDs

### Connection

**Settings**

Parameterisation	single and two push-button operation parameterisable
------------------	--

**Scope of delivery**

Bus connection included	No
-------------------------	----

**Equipment**

Number of actuation points	6
----------------------------	---

With anti-theft/dismantling protection	Yes
--	-----

Type of configuration	Beschriftungsfeld(er) - Folie
-----------------------	-------------------------------

Product type:	product type: push-button 3gang
---------------	---------------------------------

**Use**

Differentiation characteristic 1 - Sales	with labelling fields
--	-----------------------

Differentiation characteristic 3 - Sales	with horizontal operation
--	---------------------------

**Safety**

Protection index IP	IP20
---------------------	------

Protection	with dismantling protection
------------	-----------------------------

Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte
-------	---

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

Storage/transport temperature	-20...70 °C (storage at > 45°C reduces the service life)
-------------------------------	--

**Identification**

Application, usage	KNX - operating systems
--------------------	-------------------------

Product family	product family: push-button
----------------	-----------------------------

Secondary design line(s)	KNX, Berker K.1
--------------------------	-----------------