




75164085



Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 8

Measurement

Value transmitter dimming / position value transmitter 1 byte

Screen

With display No

Materials

Colour of design line anthracite

Colour anthracite

RAL colour RAL 7021 - Black grey

Material thermoplastic

Surface appearance matt

Type of surface treatment Painted

Material family Plastic

LED control

LED - KNX with green operation LED and 4 red status LEDs

Connection

Bus coupling unit for bus coupling unit flush-mounted

Scope of delivery

Bus connection included No

Equipment

Number of actuation points 8

With anti-theft/dismantling protection Yes

Product type: product type: push-button 4gang

Use

Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 3 - Sales	with vertical operation

Safety

Protection index IP	IP20
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	Radio bus - operating systems, KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker S.1/B.3/B.7
Secondary design line(s)	Berker B.7, Radio bus, Berker B.3, KNX, Berker B.1
