



75164090

**IP20**

**B.IQ push-button 4gang, KNX - B.IQ, glass p. white**

**Technical properties**

**Architecture**

Fixing mode flush-mounting

**Functions**

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

**Compatibility**

Extension unit extension unit for light scene push-button

**Controls and indicators**

With LED indication Yes

Number of buttons 4

**Dimensions**

Assembling height 16.7 mm

Height 118.1 mm

Width 88.5 mm

**Measurement**

Value transmitter dimming / position value transmitter 1 byte

**Screen**

With display No

**Materials**

Colour of design line glass polar white

Colour polarwhite

RAL colour RAL 9010 - Pure white

Material glass

Type of surface treatment Painted

Material family Glass

**LED control**

LED with blue operation LED and 8 white status LEDs

**Connection**

Bus coupling unit for bus coupling unit flush-mounted

**Scope of delivery**

Bus connection included No

**Accessories included**

Box	for installation in single standard wall boxes
Matching products	for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x, for glass frames in the same "style" for additional applications, see the Design line B.7

**Equipment**

Number of actuation points	8
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ

**Safety**

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

**Identification**

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ