




75164780



Berker S.1/B.3/B.7 Push Button 4-gang, Comfort with Label, White and Polar White

Technical properties

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 4

Operation one push-button operation for switching, pushing, shutters and dimming ; lockable via 3-button actuation ; second operating level via object or 3-button handle

Dimensions

Labelling field length (W x H) 52.3 x 24.9 mm

Height 110.7 mm

Width 56 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display No

Materials

Colour of labelling 105,105,105

Colour of design line white/polar white

Colour independent of design lines for white and polar white

Material for printing Paper

Surface appearance glossy

Type of surface treatment untreated

Material family Plastic

LED control

LED with white operation LED and 8 red status LEDs

Connection

Bus coupling unit for bus coupling unit flush-mounted

Settings

Parameterisation single and two push-button operation parameterisable

Scope of delivery

Bus connection included No

Equipment

Number of actuation points 8

With anti-theft/dismantling protection Yes

Type of configuration Beschriftungsfeld(er) - Folie

Product type: product type: push-button 4gang

Use

Differentiation characteristic 1 - Sales with labelling fields

Differentiation characteristic 3 - Sales with horizontal operation

Safety

Protection with dismantling protection

Alarm alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte

Use conditions

Operating temperature -5...45 °C

Identification

Application, usage KNX - operating systems

Product family product family: push-button

Secondary design line(s) KNX ; Berker S.1 ; Berker B.3 ; Berker B.7

Instructions

Special note text Use only in combination with frame frame with large cut-out.