



75164780



Berker S.1/B.3/B.7 Push Button 4-gang, Comfort with Label, White and Polar White

Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 4

Operation one push-button operation for switching, pushing, shutters and dimming, lockable via 3-button actuation, second operating level via object or 3-button handle

Dimensions

Labelling field length (W x H) 52.3 x 24.9 mm

Height 110.7 mm

Width 56 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display No

Materials

Colour of design line white/polar white

Colour independent of design lines for white and polar white

Colour white/polarwhite

RAL colour RAL 1013 - Oyster white

Material thermoplastic

Material for printing Paper

Type of surface treatment untreated

Material family Plastic

LED control

LED with white operation LED and 8 red status LEDs

Connection

Bus coupling unit for bus coupling unit flush-mounted

Settings

Parameterisation single and two push-button operation parameterisable

Scope of delivery

Bus connection included No

Equipment

Number of actuation points 8

With anti-theft/dismantling protection Yes

Type of configuration Beschriftungsfeld(er) - Folie

Product type: product type: push-button 4gang

Use

Differentiation characteristic 1 - Sales with labelling fields

Differentiation characteristic 3 - Sales with horizontal operation

Safety

Protection index IP IP20

Protection with dismantling protection

Alarm alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte

Use conditions

Operating temperature -5...45 °C

Identification

Application, usage KNX - operating systems

Product family product family: push-button

Secondary design line(s) KNX, Berker S.1, Berker B.3, Berker B.7

Instructions

Special note text Use only in combination with frame frame with large cut-out.