




75168690



## B.IQ push-button 4gang for light scenes, KNX - B.IQ, glass p. white

### Technical properties

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Functions

With room temperature controller	No
Light scenes	light scene push-buttons can be cascaded, retrieval, adjustment and storage of 8 light scenes

#### Controls and indicators

With LED indication	Yes
Number of buttons	4
Operation	second operating level for setting load groups via 3-button actuation

#### Dimensions

Height	118.1 mm
Width	88.5 mm

#### Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

#### Screen

With display	No
--------------	----

#### Materials

Colour of design line	glass polar white
Colour	polarwhite
RAL colour	RAL 9010 - Pure white
Material	glass
Type of surface treatment	Painted

#### LED control

LED	with blue operation LED and 8 white status LEDs (labelling field illumination)
-----	--

#### Connection

Number of load groups (increase on cascading)	8
Bus coupling unit	for bus coupling unit flush-mounted

#### Scope of delivery

Bus connection included	No
-------------------------	----

**Accessories included**

Box	for installation in single standard wall boxes
	for glass frames in the same "style" for additional applications, see the Design line B.7, for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x
Matching products	

**Equipment**

Number of actuation points	8
With anti-theft/dismantling protection	Yes
Light scenes	max. 8
Product type:	product type: B.IQ

**Safety**

Protection index IP	IP20
Protection	with dismantling protection

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

**Identification**

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ