



75168690



## B.IQ push-button 4gang for light scenes, KNX - B.IQ, glass p. white

### Technical properties

#### Functions

With room temperature controller	No
Light scenes	light scene push-buttons can be cascaded ; retrieval, adjustment and storage of 8 light scenes

#### Controls and indicators

With LED indication	Yes
Number of buttons	4
Operation	second operating level for setting load groups via 3-button actuation

#### Dimensions

Height	118.1 mm
Width	88.5 mm

#### Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

#### Screen

With display	No
--------------	----

#### Materials

Colour of design line	glass polar white
RAL colour	RAL 9010 - Pure white
Surface appearance	glossy

#### LED control

LED	with blue operation LED and 8 white status LEDs (labelling field illumination)
-----	--

#### Connection

Number of load groups (increase on cascading)	8
Bus coupling unit	for bus coupling unit flush-mounted

#### Scope of delivery

Bus connection included	No
-------------------------	----

#### Accessories included

Box	for installation in single standard wall boxes
Matching products	for glass frames in the same "style" for additional applications, see the Design line B.7 ; for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

**Equipment**

Number of actuation points	8
With anti-theft/dismantling protection	Yes
Light scenes	max. 8
Product type:	product type: B.IQ

**Safety**

Protection	with dismantling protection
------------	-----------------------------

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

**Identification**

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX ; Berker B.IQ