



75664592



B.IQ push-button 4gang thermostat, display, KNX - B.IQ, glass black

Technical properties

Functions

With room temperature controller	Yes
Function	with valve protection function
Timers	with room temperature timer and 2-week timer functions

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
Number of buttons	4
Operation	one push-button operation for switching, pushing, shutters and dimming

Dimensions

Assembling height	16.7 mm
Width of rail mounted device (RMD)	0 modules
Height	149.2 mm
Width	88.5 mm

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Screen

With display	Yes
--------------	-----

Materials

Colour of design line	glass black
RAL colour	RAL 9005 - Jet black
Material	glass
Material family	Glass

LED control

LED	with blue operation LED and 8 white status LEDs (labelling field illumination)
-----	--

Settings

Parameterisation	single and two push-button operation parameterisable
------------------	--

Accessories included

Box	for installation in single standard wall boxes
Matching products	for glass frames in the same "style" for additional applications, see the Design line B.7, for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x
Equipment	
Number of actuation points	10
Product type:	product type: B.IQ
Control	for individual single room temperature control
Software	
Update	with flash-controller technology
Safety	
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Energy efficiency class	IV (2%)
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Release issue	2.6
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ