



841952502

SCHUKO sock. outl., enh. cont. prot., screw term, Int. module inserts, pw matt

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Materials

Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	matt
Metallic colour	No

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw terminals

Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	Screw terminals

Safety

IK protection code against mechanical impacts	IK02
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes

Subject to technical modifications

Identification

Main design line	Berker Integro module inserts
Secondary design line(s)	Berker Integro Pure, Berker Integro Flow, Berker Integro Module inserts, Berker Integro Classic