



85141126

Button 1gang, Q.x, ant. velvety, lacq.

Technical properties

Controls and indicators

Operation with 2-push-buttons operation concept

Main electrical features

Nominal voltage 12 V

Voltage

Operating voltage via insert

Materials

Colour of design line anthracite

Material / workmanship lacquered

Equipment

Brightness switch-on brightness level for use on dimmer insert, power failure proof, storable

Safety

Halogen free No

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C

Energy-saving low intrinsic energy requirement

Relative humidity (without condensation) 0...65 % (without condensation)

Identification

Application, usage Light control

Main design line Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s) Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9