



85141131

Button 1gang, R.1/R.3/1930/R.cl., black glossy

Technical properties

Controls and indicators

Operation with 2-push-buttons operation concept

Main electrical features

Nominal voltage 12 V

Voltage

Operating voltage via insert

Dimensions

Diameter 57.4 mm

Materials

Colour of labelling 217,217,217

Colour of design line black

Material for printing PC-PMA black

Settings

Shading parameter R1_czarny

Laser parameter R1_schwarz

Equipment

Type of configuration Laserdruck

Brightness switch-on brightness level for use on dimmer insert, power failure proof, storable

Safety

Halogen free No

Use conditions

Operating temperature -5...45 °C

Energy-saving low intrinsic energy requirement

Relative humidity (without condensation) 0...65 % (without condensation)

Identification

Application, usage Light control

Main design line Berker R.1/R.3/R.8/Serie 1930/R.classic

Secondary design line(s) Electronics platform ; Berker R.1 ; Berker R.3 ; Berker R.8

Instructions

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!

Special note text