



85142139

Button 2gang, R.1/R.3/1930/R.cl., p. white glossy

Technical properties

Controls and indicators

Operation with 2-push-buttons operation concept per series

Main electrical features

Nominal voltage 12 V

Voltage

Operating voltage via insert

Materials

Colour of design line polar white

Colour polarwhite

Material thermoplastic

Material for printing ASA polar white

Settings

Shading parameter R1_biały

Laser parameter R1_weiß

Equipment

Type of configuration Laserdruck

Use conditions

Operating temperature -5...45 °C

Relative humidity (without condensation) 0...65 % (without condensation)

Identification

Application, usage Light control

Main design line Berker R.1/R.3/R.8/Serie 1930/R.classic

Secondary design line(s) Berker R.1, Berker R.3, Berker R.8

Instructions

Special note text

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!