



936512528

On/off switch, Integro - Design Flow/Pure, chrome matt, galvanised

Technical properties

Architecture

Type of control unit	single rocker
Number of keys	1
Fixing mode	Built-in installation

Configuration

Switch mode	1pole
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	250 V
-----------------	-------

Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	25 mm
Height	55.5 mm
Width	55.5 mm

Materials

Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material	thermoplastic
Surface appearance	matt

Connection

Type of connection	Screw connection
--------------------	------------------

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Use cases

Application	Light control
-------------	---------------

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes