



936552501

Series switch, common input terminal, Integro - Design Flow/Pure, brown m finish

Technical properties

Architecture

Type of control unit	double rocker
Number of keys	2

Configuration

Switch mode	series
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	25 mm
Height	55.5 mm
Width	55.5 mm

Materials

Surface appearance	matt
--------------------	------

Connection

Type of connection	with screw terminals
Type of connection	Screw connection

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Use cases

Application	Light control
-------------	---------------

Safety

REACH conform	Yes
RoHS conform	Yes

Identification

Appliance switch type

No

Main design line

Berker Integro Flow/Pure

Secondary design line(s)

Berker Integro Flow ; Berker Integro Pure