



936552505

Series switch, common input terminal, Integro - Design Flow/Pure, anth m

Technical properties

Architecture

Type of control unit double rocker

Configuration

Switch mode series

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 25 mm

Height 55.5 mm

Width 55.5 mm

Materials

Colour anthracite charcoal grey

RAL colour RAL 7021 - Black grey

Material thermoplastic

Surface appearance matt

Installation, mounting

Installation mode for screw fastening

Connection

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Lighting without lighting (cannot be illuminated)

Heating switch No

Use cases

Application	Light control
-------------	---------------

Safety

Protection index IP	IP20
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Identification

Appliance switch type	No
-----------------------	----

Secondary design line(s)	Berker Integro Flow, Berker Integro Pure
--------------------------	------------------------------------------