



936552510

**Series switch, common input terminal, Integro - Design Flow/Pure, black glossy**

**Technical properties**

**Architecture**

Type of control unit double rocker

**Configuration**

Switch mode series

Antibacterial treatment No

**Compatibility**

IFTTT support available No

**Controls and indicators**

Push-buttons No

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

**Electric current**

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

**Dimensions**

Depth 25 mm

Height 55.5 mm

Width 55.5 mm

**Materials**

Colour black

RAL colour RAL 9005 - Jet black

Material thermoplastic

**Installation, mounting**

Installation mode for screw fastening

**Connection**

Type of connection with screw terminals

Type of connection Screw connection

**Equipment**

Lighting without lighting (cannot be illuminated)

Heating switch No

**Use cases**

Application

Light control

**Safety**

---

Protection index IP

IP20

**Identification**

---

Appliance switch type

No

Secondary design line(s)

Berker Integro Flow, Berker Integro Pure