



936552545

Ser sw, com inp term, Integro - Design Flow/Pure, granite black silk m, lacq

Technical properties

Architecture

Type of control unit	double rocker
Number of keys	2

Configuration

Switch mode	series
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Switching current	16 AX
-------------------	-------

Dimensions

Depth	25 mm
Height	55.5 mm
Width	55.5 mm

Materials

Colour of design line	granite black
Material / workmanship	lacquered
Surface appearance	satin finish

Installation, mounting

Installation mode	for 4-hole screw fastening
-------------------	----------------------------

Connection

Terminal	common input terminal
Type of connection	with screw terminals

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Safety

Impact strength

IK05

Identification

Appliance switch type

No

Main design line

Berker Integro Flow/Pure

Secondary design line(s)

Berker Integro Flow ; Berker Integro Pure