



936552545

Ser sw, com inp term, Integro - Design Flow/Pure, granite black silk m, lacq

#### Technical properties

##### Architecture

Type of control unit	double rocker
Number of keys	2
Fixing mode	Built-in installation

##### Configuration

Switch mode	series
Antibacterial treatment	No

##### Compatibility

IFTTT support available	No
-------------------------	----

##### Controls and indicators

Push-buttons	No
--------------	----

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

##### Electric current

Switching current	16 AX
-------------------	-------

##### Dimensions

Depth	25 mm
Height	55.5 mm
Width	55.5 mm

##### Materials

Colour of design line	granite black
Colour	granite grey
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	satín finish

##### Installation, mounting

Installation mode	for 4-hole screw fastening
-------------------	----------------------------

##### Connection

Terminal	common input terminal
----------	-----------------------

Type of connection	with screw terminals
Type of connection	Screw connection
<b>Equipment</b>	
Lighting	without lighting (cannot be illuminated)
Heating switch	No
<b>Safety</b>	
Protection index IP	IP20
Impact strength	IK05
<b>Identification</b>	
Appliance switch type	No
Main design line	Berker Integro Flow/Pure
Secondary design line(s)	Berker Integro Flow, Berker Integro Pure