



936552568

Series switch, common input terminal, Integro - Design Flow/Pure, chr m, lacq

Technical properties

Architecture

Type of control unit double rocker

Configuration

Switch mode series

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 16 AX

Dimensions

Depth 25 mm

Height 55.5 mm

Width 55.5 mm

Materials

Colour of design line chrome

Colour chrome

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Material / workmanship lacquered

Material thermoplastic

Surface appearance matt

Installation, mounting

Installation mode for screw fastening

Connection

Type of connection with screw terminals

Type of connection Screw connection

Equipment	
Lighting	without lighting (cannot be illuminated)
Heating switch	No
Use cases	
Application	Light control
Safety	
Protection index IP	IP20
Impact strength	IK05
Identification	
Appliance switch type	No
Secondary design line(s)	Berker Integro Flow, Berker Integro Pure