



936552568

Series switch, common input terminal, Integro - Design Flow/Pure, chr m, lacq

Technical properties

Architecture

Type of control unit	double rocker
Number of keys	2

Configuration

Switch mode	series
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Switching current	16 AX
-------------------	-------

Dimensions

Depth	25 mm
Height	55.5 mm
Width	55.5 mm

Materials

Colour of design line	chrome
Material / workmanship	lacquered
Surface appearance	matt

Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

Connection

Terminal	common input terminal
Type of connection	with screw terminals
Type of connection	Screw connection

Equipment

Lighting	without lighting (cannot be illuminated)
----------	--

Heating switch No

Use cases

Application Light control

Safety

Impact strength IK05

Identification

Appliance switch type No

Main design line Berker Integro Flow/Pure

Secondary design line(s) Berker Integro Flow ; Berker Integro Pure