



936562509

Change-over switch, Integro - Design Flow/Pure, polar white glossy

Technical properties

Architecture

| | |
|----------------------|---------------|
| Type of control unit | single rocker |
| Number of keys | 1 |

Configuration

| | |
|-------------------------|-----------------|
| Switch mode | Off/change-over |
| Antibacterial treatment | No |

Compatibility

| | |
|-------------------------|----|
| IFTTT support available | No |
|-------------------------|----|

Controls and indicators

| | |
|--------------|----|
| Push-buttons | No |
|--------------|----|

Main electrical features

| | |
|-----------------|-------|
| Nominal voltage | 250 V |
|-----------------|-------|

Electric current

| | |
|-------------------|---|
| Switching current | 10 AX (100 W Self Ballasted Lamp (SBL)) |
|-------------------|---|

Dimensions

| | |
|--------|---------|
| Depth | 25 mm |
| Height | 55.5 mm |
| Width | 55.5 mm |

Materials

| | |
|--------------------|-----------------------|
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Surface appearance | glossy |

Installation, mounting

| | |
|-------------------|---------------------|
| Installation mode | for screw fastening |
|-------------------|---------------------|

Connection

| | |
|--------------------|----------------------|
| Type of connection | with screw terminals |
| Type of connection | Screw connection |

Equipment

| | |
|----------------|--|
| Lighting | without lighting (cannot be illuminated) |
| Heating switch | No |

Use cases

Safety

| | |
|---------------------|------|
| Protection index IP | IP44 |
| REACH conform | Yes |
| RoHS conform | Yes |

Identification

| | |
|--------------------------|---|
| Appliance switch type | No |
| Main design line | Berker Integro Flow/Pure |
| Secondary design line(s) | Berker Integro Flow ; Berker Integro Pure |
