



936572528

Intermediate switch, Integro - Design Flow/Pure, chrome matt, galvanised

Technical properties

Architecture

Type of control unit	single rocker
Number of keys	1

Configuration

Switch mode	intermediate
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Switching current	16 AX
-------------------	-------

Dimensions

Depth	25 mm
Height	55.5 mm
Width	55.5 mm

Materials

Colour of design line	chrome
Colour	chrome
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material	thermoplastic
Surface appearance	matt

Connection

Type of connection	with screw terminals
Type of connection	Screw connection

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Safety	
Protection index IP	IP20
Impact strength	IK05

Identification	
Secondary design line(s)	Berker Integro Module inserts, Berker Integro Flow, Berker Integro Pure