



936712509

**Push-button, NO contact, screw terminals, Integro - Design Flow/Pure, pol wh gl**

**Technical properties**

**Architecture**

Type of control unit single rocker

**Compatibility**

IFTTT support available No

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

**Electric current**

Momentary-contact current 10 A

**Dimensions**

Depth 25 mm

Height 55.5 mm

Width 55.5 mm

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance glossy

**Connection**

Type of connection with screw terminals

**Use cases**

Application Light control

**Use**

Differentiation characteristic 3 - Sales with screw terminals

**Safety**

Protection index IP IP44

REACH conform Yes

RoHS conform Yes

**Identification**

Main design line Berker Integro Flow/Pure

Secondary design line(s) Berker Integro Flow ; Berker Integro Pure

**Instructions**

Special note text

Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing (order no. 91853), frame with imprint "IP44" and contact protection box.