



936712518

Push-button, NO contact, screw terms, Integro - Design Flow/Pure, chr gl, galv

Technical properties

Architecture

Type of control unit single rocker

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 25 mm

Height 55.5 mm

Width 55.5 mm

Materials

Colour of design line chrome

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Material thermoplastic

Connection

Type of connection with screw terminals

Use

Differentiation characteristic 3 - Sales with screw terminals

Safety

Protection index IP IP44

Identification

Secondary design line(s) Berker Integro Flow, Berker Integro Pure

Instructions

Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing (order no. 91853), frame with imprint "IP44" and contact protection box.

Special note text