



936712524

**p-b, NO contact, screw terms, Integro - Design Flow/Pure, stain steel m, lacq**

### Technical properties

#### Architecture

Type of control unit single rocker

#### Compatibility

IFTTT support available No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

#### Electric current

Momentary-contact current 10 A

#### Dimensions

Depth 24.1 mm

Height 55.5 mm

Width 55.5 mm

#### Materials

Colour of design line stainless steel

Colour stainless steel

Colour stainless steel optics

RAL colour RAL 9022 - Pearl light grey

Material / workmanship lacquered

Material thermoplastic

Surface appearance matt

#### Installation, mounting

Installation mode for screw fastening

#### Connection

Type of connection with screw terminals

#### Use cases

Application Light control

#### Use

Differentiation characteristic 3 - Sales with screw terminals

#### Safety

Protection index IP IP44

**Identification**

---

Secondary design line(s)

Berker Integro Flow, Berker Integro Pure

**Instructions**

---

Special note text

Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing (order no. 91853), frame with imprint "IP44" and contact protection box.