



936712528

Push-button, NO contact, screw terms, Integro - Design Flow/Pure, chr m, galv

Technical properties

Architecture

Type of control unit single rocker

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 25 mm

Height 55.5 mm

Width 55.5 mm

Materials

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Material thermoplastic

Surface appearance matt

Connection

Type of connection with screw terminals

Type of connection Screw connection

Scope of delivery

With lamp No

Use

Differentiation characteristic 3 - Sales with screw terminals

Safety

Protection index IP IP44

REACH conform Yes

RoHS conform Yes

Identification

Secondary design line(s) Berker Integro Flow, Berker Integro Pure

Instructions

Special note text

Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing (order no. 91853), frame with imprint "IP44" and contact protection box.