



936712568

Push-button, NO contact, screw terms, Integro - Design Flow/Pure, chr m, lacq

## Technical properties

### Architecture

Type of control unit single rocker

### Compatibility

IFTTT support available No

### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

### Electric current

Momentary-contact current 10 A

### Dimensions

Depth 24.1 mm

Height 55.5 mm

Width 55.5 mm

### Materials

Colour of design line chrome

Colour chrome

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Material / workmanship lacquered

Material thermoplastic

Surface appearance matt

### Installation, mounting

Installation mode for screw fastening

### Connection

Type of connection with screw terminals

### Use cases

Application Light control

### Use

Differentiation characteristic 3 - Sales with screw terminals

### Safety

Protection index IP IP44

**Identification**

Secondary design line(s) Berker Integro Flow, Berker Integro Pure

**Instructions**

Special note text

Only suitable for splash-protected IP44 flush--  
mounted installation when used in conjunction with  
sealing (order no. 91853), frame with imprint "IP44"  
and contact protection box.