



941852501

SCHUKO socket outlet, with screw terminals, Integro module inserts, brown matt

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Installation depth, flush-mounted boxes 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line brown

Colour brown

Colour brown

RAL colour RAL 8017 - Chocolate brown

Material thermoplastic

Surface appearance matt

Metallic colour No

Installation, mounting

Installation mode without spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw terminals

Use

Differentiation characteristic 3 - Sales with screw terminals

Safety

| | |
|-----------------------------------------------|----|
| IK protection code against mechanical impacts | 05 |
|-----------------------------------------------|----|

| | |
|---------------------|------|
| Protection index IP | IP44 |
|---------------------|------|

| | |
|------------|-------------------------------------|
| Protection | without enhanced contact protection |
|------------|-------------------------------------|

Identification

| | |
|------------------|-------------------------------|
| Main design line | Berker Integro module inserts |
|------------------|-------------------------------|

| | |
|--------------------------|-------------------------------------------------------------------------------------------------|
| Secondary design line(s) | Berker Integro Module inserts, Berker Integro Classic, Berker Integro Flow, Berker Integro Pure |
|--------------------------|-------------------------------------------------------------------------------------------------|

Instructions

| | |
|-------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing (order no. 91853), frame with hinged lid (imprint "IP44") and contact protection box. |
|-------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|