



947782502

SCHUKO socket outlet, w. plug-in term.s, Int. module inserts, polar white matt

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32.7 mm

Installation depth, flush-mounted boxes 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line polar white

Colour polarwhite

Colour white

Surface appearance matt

Metallic colour No

Installation, mounting

Installation mode without spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Contact contacts made of copper alloy

Use

Differentiation characteristic 3 - Sales with plug-in terminals

Safety

| | |
|---|---|
| IK protection code against mechanical impacts | 05 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |
| Protection | without enhanced contact protection |
| Identification | |
| Main design line | Berker Integro module inserts |
| Secondary design line(s) | Berker Integro Module inserts ; Berker Integro Classic ; Berker Integro Flow ; Berker Integro Pure |
| Instructions | |
| Special note text | Only suitable for splash-protected IP44 flush--mounted installation when used in conjunction with sealing (order no. 91853), frame with hinged lid (imprint "IP44") and contact protection box. |