



947782502

SCHUKO socket outlet, w. plug-in term.s, Int. module inserts, polar white matt

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	Built-in installation

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32.7 mm
Installation depth, flush-mounted boxes	32 mm

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	matt
Material / surface	duroplast base, thermoplastic centre plate, matt
Metallic colour	No

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals
Contact	contacts made of copper alloy

Use

Differentiation characteristic 3 - Sales

with plug-in terminals

Standards

Standard

NEN 1010

Safety

IK protection code against mechanical impacts

05

Protection index IP

IP44

REACH conform

Yes

RoHS conform

Yes

Halogen free

No

Protection

without enhanced contact protection

Identification

Main design line

Berker Integro module inserts

Secondary design line(s)

Berker Integro Module inserts, Berker Integro Classic, Berker Integro Flow, Berker Integro Pure

Instructions

Special note text

Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing (order no. 91853), frame with hinged lid (imprint "IP44") and contact protection box.