



BA7A100040

**Slotted panel trunking made of PVC BA7A 100x40mm grey**

**Technical properties**

**Architecture**

Flexible No

**Configuration**

Side wall configuration Slotted

**Electric current**

Current leak stable Yes

**Dimensions**

Trunking height 100 mm

Length 2000 mm

Trunking width 40 mm

Slot width 6 mm

Tongue width 6.5 mm

**Cover, door**

Lid shape loose

**Materials**

Material group plastic

**Installation, mounting**

Base punching EN 50085-2-3:1999

Fixing type bottom punching

**Cable**

Number of wires 1,5 mm<sup>2</sup> - 40% filling degree 125

Internal/useful cross section 3328 mm<sup>2</sup>

Number of wires 2,5 mm<sup>2</sup> - 40% filling degree 89

Number of wires 1,0 mm<sup>2</sup> - 40% filling degree 173

**Standards**

Approvals EN50085-2-3

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

