



BA7A60025

Slotted panel trunking made of PVC BA7A 60x25mm grey

Technical properties

Architecture

Flexible No

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 60 mm

Length 2000 mm

Trunking width 25 mm

Width of installed product 25 mm

Slot width 6 mm

Tongue width 6.5 mm

Cover, door

Lid shape loose

Materials

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching EN 50085-2-3:1999

Fixing type bottom punching

Cable

Number of wires 1,5 mm² - 40% filling degree 39

Internal/useful cross section 1045 mm²

Number of wires 2,5 mm² - 40% filling degree 28

Number of wires 1,0 mm² - 40% filling degree 54

Standards

Approvals EN50085-2-3

European directive RoHS voluntary compliance

UL 94 classification V0

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Fireproof classification	M1

temperatur

Ambient temperature	-5...60 °C
---------------------	------------