



BA7A60120

Slotted panel trunking made of PVC BA7A 60x120mm grey

Technical properties

Architecture

Flexible No

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 60 mm

Length 2000 mm

Trunking width 120 mm

Slot width 6 mm

Tongue width 6.5 mm

Cover, door

Lid shape loose

Materials

Colour stone grey

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching EN 50085-2-3:1999

Cable

Number of wires 1,5 mm² - 40% filling degree 211

Internal/useful cross section 5558 mm²

Number of wires 2,5 mm² - 40% filling degree 151

Number of wires 1,0 mm² - 40% filling degree 294

Standards

European directive RoHS voluntary compliance

UL 94 classification V0

Safety

Fireproof classification M1

