



BA7A80060

## Slotted panel trunking made of PVC BA7A 80x60mm grey

### Technical properties

#### Architecture

Flexible No

#### Configuration

Side wall configuration Slotted

#### Electric current

Current leak stable Yes

#### Dimensions

Trunking height 80 mm

Length 2000 mm

Trunking width 60 mm

Slot width 6 mm

Tongue width 6.5 mm

#### Cover, door

Lid shape loose

#### Materials

Material group plastic

Type of surface treatment untreated

#### Installation, mounting

Base punching EN 50085-2-3:1999

Fixing type bottom punching

#### Cable

Number of wires 1,5 mm<sup>2</sup> - 40% filling degree 152

Internal/useful cross section 3848 mm<sup>2</sup>

Number of wires 2,5 mm<sup>2</sup> - 40% filling degree 109

Number of wires 1,0 mm<sup>2</sup> - 40% filling degree 211

#### Standards

Approvals EN50085-2-3

European directive RoHs voluntary compliance

UL 94 classification V0

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Fireproof classification	M1
<b>temperatur</b>	
Ambient temperature	-5...60 °C