



EE815B



**Presence detector 360° monobloc, flush mounted, black**

**Technical properties**

**Main electrical features**

Frequency 50/60 Hz

**Power**

Halogen switching capacity 230V 2300 W

Max. power with fluo uncompensated lamps 1000 W

Incandescent bulb power 2300 W

Maximum power per output for low-voltage halogen lamps with conv. transformer 1500 W

**Power supply**

Supply voltage 230 V +10% / -15%

**Materials**

Colour white

**Lighting control**

Brightness measurement range 5 / 1000 Lux

**Settings**

Response value sensitivity adjustable No

**Equipment**

Remote controllable EE807, EE808

**Safety**

Protection class isol.class II