




EE815B

IP41



Presence detector 360° monobloc, flush mounted, black

Technical properties

Main electrical features

Frequency 50/60 Hz

Power

Halogen switching capacity 230V 2300 W

Max. power with fluo uncompensated lamps 1000 W

Incandescent bulb power 2300 W

Maximum power per output for low-voltage halogen lamps with conv. transformer 1500 W

Power supply

Supply voltage 230 V +10% / -15%

Materials

Colour white

Lighting control

Brightness measurement range 5 / 1000 Lux

Settings

Response value sensitivity adjustable No

Equipment

Remote controllable EE807, EE808

Safety

Protection class isol.class II