



EW032_C

Industrial contactor 32A-AC3 / coil 220V 50-60Hz

Technical properties

Architecture

Type of pole	3 P
--------------	-----

Main electrical features

Rated operational voltage Ue	690 V
Type of supply voltage	AC

Voltage

Rated insulation voltage	1000 V
DC control voltage	0 V
Command voltage AC	220 V

Electric current

Acceptable current rating with AC1	50 A
Rated current	32 A
Thermal rated current outside of housings	50 A
Rated operational current in AC3	32 A

Dimensions

Depth of installed product	92 mm
Height of installed product	72 mm
Width of installed product	55 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Contact rating with 400 V in AC3	15 kW
----------------------------------	-------

Endurance

Electric endurance in number of cycles	500000
Number of mechanical operations	5000000

Connection

Connection cross-section of input and output with screws, for massive conductors	4 / 10 mm ²
Connection cross section of access and exit with screws, for flexible conductor	4 / 10 mm ²

Equipment

Number of auxiliary contacts as normally closed contact	1
---	---

Number of auxiliary contacts as normally open contact	1
Quantity of NC contacts	0
Quantity of NO contacts	3
Use cases	
Category of use	AC3
Standards	
Standard text	IEC 60947-4-1
European directive WEEE	not concerned
Use conditions	
Operating temperature	-20...55 °C
Altitude	2000 m
Storage/transport temperature	-40...80 °C
Relative humidity (without condensation)	45...85 %